

QuickTask™ 0200/0250 Flat Mop Head

Mult-Layer Knitted Polyester Mop Head

Description

The QuickTask range consists of a variety of flat mop heads that can be easily attached to a choice of flat mop head frame and handle assemblies. The flat mop heads are compatible with the QuickTask hinged mop frames 2749 (stainless steel) and 2740 (autoclavable polypropylene).

QuickTask TASK0200 and TASK0250 mop heads are constructed from multi-layers of 100% knitted polyester creating a highly sorbent mop which allows for an even application of solution. The cleanroom laundered polyester ensures a very low level of particulates making the mop suitable for use in the highest grade of cleanroom.

Designed for single use, the mop heads are compatible with a range wide of chemicals and disinfectants. The TASK0250 is provided sterile by gamma irradiation, at no less than 25kGy per AAMI guidelines.

Technical Data

Mop head component materials (cleaning surface first)	100% knitted polyester fabric
Construction	Multi-layer sewn lamination
Dimensions; inches (cm)***	
As Packaged; Nominal:	15" x 4.75" (38x12cm)
Mounted on Frame:	16" x 5" (41x13cm)

Attribute; (units)	Value**	Test Method
Mop weight, dry; (g/mop)	70	Contec Method
Sorbency, IPA/water, (mL/mop)	330	CTM005
Non-volatile residue, NVR		IEST-RP-CC004.2, Sec. 6.1.2
In deionised water; (g/mop)	ND	
In isopropanol; (g/mop)	0.008	
Particles ≥ 0.5µm; (x10 ⁶ /mop)	0.65	IEST-RP-CC004.2, Sec. 5.2
Fibers > 100µm; (10 ³ /mop)	0.02	IEST-RP-CC004.2, Sec. 5.2

** ND = None detected; levels are below detection limit of test equipment

*** Note: Dimensions determined were made when mop was mounted on head frame #2749 and will vary based on the head frame used.

Part Number	Description	EA/OB1	OB1/CS	EA/CS
TASK0200	QuickTask Mop Head, 100% polyester flat	4	12	48

Part Number	Description	EA/OB1	OB1/OB2	OB2/OB3	OB3/CS	EA/CS
TASK0250	QuickTask Mop Head, 100% polyester, sterile	1	1	4	10	40


EA = Each, OB1 = Outer Bag 1, OB2 = Outer Bag 2, OB3 = Outer Bag 3, CS = Case

Notes:

- 1) The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 10/15/15





Technical Data

Notes:

- 1) The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 10/15/15



North America
P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
www.contecinc.com

Europe
ZI du Prat – RP 3707
56037 VANNES Cedex
FRANCE
+33 297 437 690

China
No.17 Longyun Road
Suzhou 215024
CHINA
+ 86-512-6274 4050