



## Technical Data

### **CONSTIX<sup>®</sup> Swabs** **SC Series Cotton Swabs** **(Part Numbers: SC-1, SC-2, SC-3, SC-4, SC-7, SC-9)**

#### **Description**

The SC Series cotton swabs consist of high quality, long staple-length cotton, tightly wrapped and shaped on both ends of high strength, wound paper handles (except the SC-9 which has a wood handle). The heads are held to the handles using a methyl-cellulose binder.

The high quality cotton fibers provide excellent particle entrapment and retention, as well as exceptional absorbency of most solvents and solutions. The heads are very tightly wrapped and shaped using methyl-cellulose binder which minimizes fiber shedding, while maintaining low levels of extractable residue. The SC series cotton swabs are absorbent to most common solvents including isopropyl alcohol, acetone, and is ideal for use with aqueous based solutions.

#### **Physical Information**

##### Dimensions:

SC-1	0.20" dia. x 0.5" pointed/pointed double-ended cotton swab, paper handle, 3" total length
SC-2	0.20" dia. x 0.6" round/round double-ended cotton swab, paper handle, 3" total length
SC-3	0.10" dia. x 0.5" round/round double-ended cotton swab, paper handle, 3" total length
SC-4	0.08" dia. x 0.3" hard sharp point double-ended cotton swab, paper handle, 3" total length
SC-7	0.10" dia. x 0.4" sharp point double-ended cotton swab, paper handle, 3" total length
SC-9	0.20" dia. x 0.6" single round cotton swab, wood handle, 6" total length

##### Packaging:

SC-1	25 swabs/cellophane sleeve, 50 sleeves/box, 3 boxes/case (3,750 swabs/case)
SC-2	25 swabs/cellophane sleeve, 50 sleeves/box, 3 boxes/case (3,750 swabs/case)
SC-3	25 swabs/cellophane sleeve, 100 sleeves/box, 2 boxes/case (5,000 swabs/case)
SC-4	25 swabs/cellophane sleeve, 100 sleeves/box, 2 boxes/case (5,000 swabs/case)
SC-7	25 swabs/cellophane sleeve, 100 sleeves/box, 2 boxes/case (5,000 swabs/case)
SC-9	100 swabs/poly bag, 10 bags/box, 2 boxes/case (2,000 swabs/case)

#### **Technical Data**

Specific technical data available upon request.

##### Notes:

- 1) Data shown are typical values and should not be used as product specifications.
- 2) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 3) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 06/20/05



P.O. Box 530  
Spartanburg, SC 29304 USA  
Phone: +1-864-503-8333  
Fax: +1-864-503-8444  
Toll free US, Canada, PR: 1-800-289-5762

**Customer Service**  
United States: 1-866-855-4682  
Europe/Asia: +1-864-699-8257  
e-mail: wipers@contecinc.com  
www.contecinc.com